


BUCK CONVERTER

Step-down converter for voltages up to 35 V



This is a voltage converter based on the DC-DC module LM2596S. The voltage can be adjusted by the potentiometer with an accuracy of ± 0.1 V. The integrated segment display can additionally be switched between the input and the output voltage via the button.

MAIN FEATURES

Switching regulator	LM2596S
Special features	Adjustment via potentiometer, Control via segment display
Weight	22 g
Dimensions	67 x 37 x 15 mm
Items shipped	Buck converter

SPECIFICATIONS

Input voltage	4 - 35 V
Input current	≤ 2 A
Output voltage	3 - 34 V
Output current	≤ 2 A
Output power	Max. 15 W
Accuracy	$\pm 0,1$ V

ADDITIONAL INFORMATION

Article no.	SBC-Buck01
EAN	4250236823706
Customs Tariff No.	85044030