

# LogiLink®



USB-C™ 20 W PD  
Power Adapter

Art. No.: PA0261



## Compact & Powerful

Rapidly charge your devices with 20 W USB-C Power Delivery; it is compact and lightweight for easy portability and storage. Keep your devices charged at home, in the office, or on-the-go.



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



**USB-C  
Power Delivery**



20W output for a variety of devices from tablets to smartphones; it powers your devices at incredible speeds.



Extremely safe-comes with overload, overvoltage, overtemperature, overcurrent and short-circuit protection.



Compact size makes it lightweight and easily fits into your laptop bag or backpack. The perfect mobile accessory for traveling.



Wide compatible with most USB-C devices such as smartphones, tablets and much more.



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



Made in China

# Quickly Charging ⚡ in a Short Time



## Specification:

Input	230 V AC 50/60 Hz 0.6 A
Output	5 V/3 A (15 W), 9 V/2.22 A (20 W), 12 V/1.67 A (20 W) Max. total output: 20 W
Efficiency	Level VI
Operating Temperature	0–45 °C
Storage Temperature	-20–85 °C
Relative Humidity	10–80% (non-condensing)
Storage Humidity	10–93% (non-condensing)
Dimensions	9x5.1x2.6 cm
Weight	59 g



## Package Content:

- » 1x USB-C 20W PD Power Adapter
- » 1x User Manual

## Package Information:

- » Packing Dimension: 138x75x30 mm
- » Packing Weight: 0.083 kg
- » Carton Dimension: 335x315x167 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 3.82 kg



⚠ Proper use of the PD function can only be guaranteed in combination with certified USB cables with E-Mark chipset.

\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



Made in China