

LogiLink®

Dual-Port USB Car Charger, 10.5W

Art. No.: PA0227



Fast charging 2-port USB car charger for any phones or tablets on the road.



Efficient High-Speed Charging

Dual ports with 10.5W outputs charging your power-hungry devices at high speeds simultaneously.



Multiple Protection

Supports overcurrent, overvoltage, overheating and short circuit protections.

Best Connectivity



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



Made in China

LogiLink®



Dual-Port USB Car Charger,
10.5W

Art. No.: PA0227



Universal Compatibility

Compatible with 5V devices such as iPhone, iPad, mobile devices, tablets and power banks.

Best Connectivity



RoHS
compliant



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



PA0227



Made in China

LogiLink®



Dual-Port USB Car Charger, 10.5W

Art. No.: PA0227

Specification:

Input	DC 12/24V
Output	5V/2.1A (10.5W)
USB Port	2 ports
Protections	Overcurrent, overvoltage, overheating and short circuit
Ripple And Noise	≤80mV
Operating Temperature Range	0~40°C
Storage Temperature Range	-40°C ~ 85°C
Relative Humidity	25% ~ 90% (non-condensing)
Storage Humidity	10%~90% (non-condensing)
Standby Power Loss	0.1W
Dimension	Ø32 x 64mm
Weight	52g



Package Contents:

- » 1 x Dual-Port USB Car Charger
- » 1 x User Manual

Package Information:

- » Packing Dimension: 95 x 75 x 40mm
- » Packing Weight: 0.04kg
- » Carton Dimension: 420 x 320 x 140mm
- » Carton Q'ty: 40pcs
- » Carton Weight: 2.3kg

WARNING

Remove any device attached on the adaptor before starting the car to avoid damage to the electronic device.
Please check your gadget power requirement and compatibility.



RoHS
compliant



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



PA0227



Made in China