

Polyester Braided Sleeving (bulk stock) Item-No.: 22CA162...166 / 23CA170, 171, 248, 249



This cable bundling sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites. The tightly woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends. It is possible to lead out individual cables on the track through the slot.

To prevent fraying, the sleeve should be cut with a hot cutting tool!

Technical data: Material: polyester braid • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • Tensile strength max. 10.4 MPa • RoHS compliant, REACH compliant, halogen free • Flammability class: UL94HB.

Item-No.	GTIN	Content	Bundle Ø min.	Bundle Ø max.	Complete reel Content / max. length
22CA162	4260732281412	1 m +	3 mm	4 mm	100 m
22CA163	4260732281429	1 m +	6 mm	7 mm	100 m
22CA164	4260732281436	1 m +	9 mm	10 mm	100 m
22CA165	4260732281443	1 m +	13 mm	14 mm	100 m
22CA166	4260732281450	1 m +	19 mm	20 mm	50 m
23CA170	4260732283669	1 m +	25 mm	26 mm	50 m
23CA171	4260732283676	1 m +	32 mm	33 mm	50 m
23CA248	4260732285205	1 m +	38 mm	39 mm	25 m
23CA249	4260732285212	1 m +	50 mm	51 mm	25 m