

## Data Sheet

### Carbon film resistor set, axial lead 5 %



#### Technical data

Type: Carbon film resistor assortment ( 10Ω - 820Ω )

Tolerance: ± 5%

Leaded Type: Axial

Box Length: 265 mm

Box Width: 182 mm

Box Height: 17.5 mm

Box Material: PP

#### Inventory:

No.	Description	Q'ty	No.	Description	Q'ty
1	10 OHM 1/4W ±5%	25	13	33 OHM 1/4W ±5%	25
2	100 OHM 1/4W ±5%	25	14	330 OHM 1/4W ±5%	25
3	12 OHM 1/4W ±5%	25	15	39 OHM 1/4W ±5%	25
4	120 OHM 1/4W ±5%	25	16	390 OHM 1/4W ±5%	25
5	15 OHM 1/4W ±5%	25	17	47 OHM 1/4W ±5%	25
6	150 OHM 1/4W ±5%	25	18	470 OHM 1/4W ±5%	25
7	18 OHM 1/4W ±5%	25	19	56 OHM 1/4W ±5%	25
8	180 OHM 1/4W ±5%	25	20	560 OHM 1/4W ±5%	25
9	22 OHM 1/4W ±5%	25	21	68 OHM 1/4W ±5%	25
10	220 OHM 1/4W ±5%	25	22	680 OHM 1/4W ±5%	25
11	27 OHM 1/4W ±5%	25	23	82 OHM 1/4W ±5%	25
12	270 OHM 1/4W ±5%	25	24	820 OHM 1/4W ±5%	25