

Data Sheet

Compressed air hose



Length: 100 m

Item no.	Model no.	Material	Outer Diameter	Inner diameter	Max. working pressure	Operating temperature	Color
2615604	PU4X2.5	Polyurethane	4 mm	2.5 mm	10 bar	-20 – 80 °C	Blue
2615605	PU6X4	Polyurethane	6 mm	4 mm	10 bar	-20 – 80 °C	Blue
2615606	PU8X5	Polyurethane	8 mm	5 mm	10 bar	-20 – 80 °C	Blue
2615607	PU8X5.5	Polyurethane	8 mm	5.5 mm	10 bar	-20 – 80 °C	Blue
2615608	PU10X6.5	Polyurethane	10 mm	6.5 mm	10 bar	-20 – 80 °C	Blue
2615609	PU12X8	Polyurethane	12 mm	8 mm	10 bar	-20 – 80 °C	Blue
2615610	PTFE4X2	PTFE	4 mm	2 mm	10.2 bar	-80 – 200 °C	Blue
2615611	PTFE6X4	PTFE	6 mm	4 mm	10.2 bar	-80 – 200 °C	Blue