

3.5" Single HDD Mobile Rack

1 HDD



Model	N-11WM
Form Factor	1 x 5.25" Drive Bay
Support HDD	3.5" SATA 6G & SAS 12G HDD
Signal Control	1 x 7pin SATA
Power Control	1 x 15pin SATA + 1 x 4pin
Security Design	Dual-Function Metal Key Lock Power & Mechanical Lock
Material	Aluminum Body
LED Indication	Power on-Green/ HDD Accessing- Orange
Fan	1 x 4cm Fan
Dim & Weight	188.5(L) X 146(W) X 42(H) mm/ 0.73kg

6G Version : S-11WM (ST-135)



Model	N-16TM
Form Factor	1 x 5.25" Drive Bay
Support HDD	2.5" /3.5" SATA 6G & SAS 12G HDD/ SSD
Signal Control	1 x 7pin SATA
Power Control	1 x 15pin SATA
Security Design	Metal Key Lock
Material	Aluminum Body & Tray
LED Indication	Power on-Green/ HDD Accessing- Orange
Fan	(Optional)
Dim & Weight	187(L) X 147(W) X 42(H) mm/ 0.43kg

6G Version : S-16TM

12G Power Button Version : N-16TM Pro



Upon request

Trayless

Model	N-16TL
Form Factor	1 x 5.25" Drive Bay
Support HDD	3.5" SATA 6G & SAS 12G HDD
Signal Control	1 x 7pin SATA
Power Control	1 x 15pin SATA
Security Design	Metal Key Lock
Material	Aluminum Body & Bezel
LED Indication	Power on-Blue/ HDD Accessing- Purple
Fan	(Optional)
Dim & Weight	180(L) X 146(W) X 42(H) mm/ 0.28kg

6G Version : S-16TL

12G Power Button Version : N-16TL Pro



HDD Carrier for N-11WM / S-11WM
T-11A
For 3.5" HDD Carrier,with Fan
Aluminum Body & Plastic Handle
Dim:170.5(L) x 121.6(W) x 41.5(H) mm



HDD Carrier for N-16TM / S-16TM
T-12A
For 2.5" / 3.5" HDD Carrier
Aluminum Body & Handle
Dim:159.5(L) x 113.5(W) x 26.5(H) mm

