

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

MF-80 PINLESS MOISTURE METER



Item no: 2620275

The product is a handheld pinless moisture meter. Use it to scan for moisture without physically penetrating the surface.

CONTENTS

Moisture meter // 3x AAA 1.5 V batteries // Carry bag // Operating instructions

TECHNICAL DATA

Power supply	3x AAA 1.5 V batteries
Auto shut-off	15 mins
Ingress protection	IP54
Measuring range	0.0 - 100.0
Resolution	0.5
Penetration depth	20 - 40 mm
Operating altitude	≤2000 m
Operating conditions	0 °C to +50 °C
Storage conditions	-10 °C to +60 °C <80 % RH (non-condensing)
Dimensions (W x H x D)	48.5 x 206 x 27 mm
Weight	155 g



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2620275_V1_1123_en_ds 1110907659 11/01 en