

Spiral Coiled Hose

No.: 2111C141 ... 2112C146



This set with flexible and robust spiral tubing is ideal for creating clarity, order and safety in cable routing. Apart from applications in the office or living room, applications in control cabinets or boats, caravans and even the prevention or reduction of animal bites on exposed cables are also conceivable. The spiral hose can securely hold cables together in the respective bundle diameter.

Furthermore, this is a quality product that meets the latest requirements and can be used in standard applications without hesitation. Due to the structure, it is possible to attach the protective conduit to existing cables afterwards or to "lead out" individual cables on the way. Shortening or cutting into pieces is also no problem. No special tools required.

Technical data: Material: PE • Bundle diameter range: 3 ... 70 mm • Hose length: 10 m • Operating temperature range: -55 ... +80 °C • Lead-free • Halogen-free • RoHS-compliant • CE • Flammability class: UL94HB.

Part No.	GTIN	Content	Bundle Ø min.	Bundle Ø max.	Color
2111C141	4260732280309	10 m	3 mm	25 mm	White
2111C142	4260732280316	10 m	4 mm	50 mm	White
2111C143	4260732280323	10 m	12 mm	70 mm	White
2111C144	4260732280330	10 m	3 mm	25 mm	Black
2111C145	4260732280347	10 m	4 mm	50 mm	Black
2111C146	4260732280354	10 m	12 mm	70 mm	Black