

CU-Wire Set 10 Colors

No.: 22CW001 ... 22CW007



The stranded wire assortment includes ten flexible copper strands in a bag. This means that everything is clearly arranged and tidy - and therefore easy to handle. The colored PVC sheathing covers the copper braiding and ensures high dielectric strength as well as differentiation of the cores.

Technical data: Material: PVC insulation, copper wire • Rated voltage: 230 V AC/DC • Operating temperature range: -30 ... +70 °C • Lead-free • Halogen-free • RoHS-compliant • Colors in Set: white, blue, brown, orange, green, yellow, gray, purple, black, red.

Part No.	GTIN	Content per color	Cross section	Structure CU wire	Outer diameter
22CW001	4260732280583	10 m (10x)	0.14 mm ²	18 x 0.1 mm	1.2 mm
22CW002	4260732280361	10 m (10x)	0.25 mm ²	8 x 0.2 mm	1.2 mm
22CW003	4260732280743	10 m (10x)	0.34 mm ²	11 x 0.2 mm	1.5 mm
22CW004	4260732280750	5 m (10x)	0.50 mm ²	16 x 0.2 mm	1.8 mm
22CW005	4260732280767	5 m (10x)	0.75 mm ²	24 x 0.2 mm	2.0 mm
22CW006	4260732280774	5 m (10x)	1.00 mm ²	32 x 0.2 mm	2.1 mm
22CW007	4260732280781	5 m (10x)	1.50 mm ²	30 x 0.25 mm	2.6 mm