

TECHNICAL DATA SHEET

www.quadrios.de

& Crimping Pliers for Ferrules & Crimp Connector Assortment 850 pcs Bundle Item-No.: 22T014



This multifunction crimping pliers is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The tool provides a lot of options and is made of high quality materials.

Technical Specifications

Size: 190 x 135 mm • Material: carbon steel S50C, handle PP/TPR • Crimping function for terminals (insulated) 0.25 mm² ... 2.5 mm² (24 ... 14 AWG) • Pressure adjustment for actuation force.



Illustration similar

Ratchet crimp technology provides repeatable and reliable terminations Pressure adjustment for actuation force Crimp release provides Operator's safety Ergonomic handle provides grip and maximum leverage

Contained inserts

Application by qualified electricians only.

Insert for insulated terminals 0.25...2.5 mm² • Insert for wire end ferrules 0.25...6 mm² • Insert for flat receptacles / flat plugs (uninsulated) 0.5...1.5 mm² • Insert for MC4 solar plugs 2.5...6 mm² • Hex wrench • 4 x spare screws.



Insulated Terminals



Ferrules



Flat Plugs



Solar Plugs



TECHNICAL DATA SHEET

www.quadrios.de

Crimp connector assortment 850 pcs



Fork connectors, ring terminals, ferrules, blade receptables, isolating sleeves, flat plugs

Bundle Item No. 22T014



Quadrios crimp connectors guarantee optimal results in conjunction with fitting crimping tools. This product series includes the most common parts used in practice. The assortment is especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

Content	Description	Material	Cross section
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Ring terminal yellow, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
80 pcs	Ferrules white, length 14 mm	Copper, tin plated	0.5 mm ²
75 pcs	Ferrules green, length 14.3 mm	Copper, tin plated	1.0 mm ²
55 pcs	Ferrules yellow, length 14.3 mm	Copper, tin plated	1.5 mm ²
40 pcs	Ferrules black, length 17.4 mm	Copper, tin plated	2.5 mm ²
25 pcs	Ferrules blue, length 19.4 mm	Copper, tin plated	4.0 mm ²
15 pcs	Ferrules red, length 20.5 mm	Copper, tin plated	6.0 mm ²
60 pcs	Blade receptacle 2.8 mm	Copper, tin plated	0.5 mm ²
50 pcs	Blade receptacle 4.8 mm	Copper, tin plated	0.5 mm ²
30 pcs	Blade receptacle 6.3 mm	Copper, tin plated	1.5 mm ²
60 pcs	Flat plug 2.8 mm	Copper, tin plated	0.5 mm ²
50 pcs	Flat plug 4.8 mm	Copper, tin plated	0.5 mm ²
30 pcs	Flat plug 6.3 mm	Copper, tin plated	1.5 mm ²
60 pcs	Isolating sleeve transparent 2.8 mm	PVC	//
50 pcs	Isolating sleeve transparent 4.8 mm	PVC	//
30 pcs	Isolating sleeve transparent 6.3 mm	PVC	//

Connection only by qualified electricians!