

www.quadrios.de

Maxi-Set Crimping Pliers, Automatic Multifunction Wire Stripper & Accessories Bundle Item-No.: 22T016

REACH Compliant

This multifunction crimping pliers is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The tool provides a lot of options and is made of high quality materials.

Technical Specifications

Size: 190 x 135 mm • Material: carbon steel S50C, handle PP/TPR • Crimping function for terminals (insulated) 0.25 mm² ... 2.5 mm² (24 ... 14 AWG) • Pressure adjustment for actuation force.



Illustration similar

Inserts change quick and easy with a hex-key Black oxide satin finish, heat treat, high quality steel Ratchet crimp technology provides repeatable and reliable terminations Pressure adjustment for actuation force Crimp release provides Operator's safety Ergonomic handle provides grip and maximum leverage

Contained inserts

Application by qualified electricians only.

Insert for insulated terminals 0.25...2.5 mm² • Insert for wire end ferrules 0.25...6 mm² • Insert for flat receptacles / flat plugs (uninsulated) 0.5...1.5 mm² • Insert for MC4 solar plugs 2.5...6 mm² • Hex wrench • 4 x spare screws.



Insulated Terminals



Ferrules



Flat Plugs



Solar Plugs



www.quadrios.de

Self Adjusting Wire-End Ferrule Crimping Pliers Range 0.25...10 mm² Bundle Item-No.: 22T016


This crimping tool is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The crimping tool is optimally matched to the field of application and has an automatic adjustment to the sleeve diameters between 0.25 and 10 qmm. The square crimping claw ensures a safe crimping process, the ergnonmic handle fits well in the hand and allows comfortable working. The pliers have an adjustment option for fine adjustment of the compressive force and a quick locking safety lock.



Technical Specifications

Four-mandrel press claw • Automatic adjustment • Fine adjustment ratchet pressure • Quick release safety lock • ergonomic handle • Range from 0.25 to 10 mm².

Usage example



Application by qualified electricians only.

Works best with Quadrios`ferrule assortment sets.





www.quadrios.de

Automatic multifunction wire stripper Bundle Item-No.: 22T016

Electroplating environmental protection Zinc-based alloys



Stripping jaws can strip wire from 0,25...6 mm² (10...24 AWG)



Technical Specifications

Size: 210 x 108 mm • Material: carbon steel S50C, handle PP/TPR • Stripping function for cable, cross section: 10 ... 24 AWG / 0.25 ... 6 mm² • Wire cutter function for copper and aluminum wires • Crimping function for terminals (insulated/uninsulated) 10 ... 22 AWG / 0.5 ... 6 mm² • Crimp function for ignition terminals 7 / 8 mm².

Application by qualified electricians only.



www.quadrios.de

Ferrule assortment 1200 pcs (DIN color code) Bundle Item-No.: 22T016

These ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

The assortment contains a 1200-piece premium ferrule set (DIN color code) for an application range of cable cross sections from 0.5 to 10 qmm. Optimal for use with suitable wire end ferrule crimping pliers.





Technical Specifications

Voltage (max.): 440 V, Material: polyamide, copper alloy. The ferrules comply with RoHS directives and are CE compliant. Further technical data on the included components are noted in the data sheet. Installation by qualified electricians only.

Content

Practical assortment box, 25 ferrules yellow 6 qmm (10 AWG), 25 ferrules red 10 qmm (7 AWG), 50 ferrules grey 4 qmm (12 AWG), 250 ferrules blue 2,5 qmm (14 AWG), 250 ferrules black 1.5 qmm (16 AWG), 200 ferrules gray 0.75 qmm (20 AWG), 200 ferrules red 1 qmm (18 AWG), 200 ferrules white 0.5 qmm (22 AWG).



www.quadrios.de

Crimp connector assortment 500 pcs set



Fork connectors, ring terminals, blade receptables, flat plugs, round plugs, round plug sleeves

Bundle Item-No. 22T016



Quadrios crimp connectors guarantee optimal results in conjunction with fitting crimping tools. This product series includes the most common parts used in practice. The assortment is especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

Content	Description	Material	Cross section
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Ring terminal red, hole@ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Blade receptacles red, 2.8 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Blade receptacles blue, 4.8 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Blade receptacles yellow, 6.3 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Flat plug red, 2.8 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Flat plug blue, 4.8 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Flat plug yellow, 6.3 mm	Copper, tin plated	1.52.5 mm ²
20 pcs	Round plug red, Ø 4 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Round plug sleeve red, Ø 4 mm	Copper, tin plated	1.52.5 mm ²
20 pcs	Round plug blue, Ø 4 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Round plug sleeve blue, Ø 4 mm	Copper, tin plated	1.52.5 mm ²

Connection only by qualified electricians!



www.quadrios.de

Crimp connector assortment 850 pcs



Fork connectors, ring terminals, ferrules, blade receptables, isolating sleeves, flat plugs

Bundle Item-No. 22T016



Quadrios crimp connectors guarantee optimal results in conjunction with fitting crimping tools. This product series includes the most common parts used in practice. The assortment is especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

Content	Description	Material	Cross section
25 pcs	Fork connector red, hole@ 3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
25 pcs	Ring terminal red, hole@3.1 mm	Copper, tin plated	0.51.5 mm ²
25 pcs	Ring terminal blue, hole@4.1 mm	Copper, tin plated	0.51.5 mm ²
20 pcs	Ring terminal yellow, holeØ 5.2 mm	Copper, tin plated	1.52.5 mm ²
80 pcs	Ferrules white, length 14 mm	Maria de la companya della companya	0.5 mm ²
75 pcs	Ferrules green, length 14.3 mm	Copper, tin plated	1.0 mm ²
55 pcs	Ferrules yellow, length 14.3 mm	Copper, tin plated	1.5 mm ²
40 pcs	Ferrules black, length 17.4 mm	Copper, tin plated	2.5 mm ²
25 pcs	Ferrules blue, length 19.4 mm	Copper, tin plated	4.0 mm ²
15 pcs	Ferrules red, length 20.5 mm	Copper, tin plated	6.0 mm ²
60 pcs	Blade receptacle 2.8 mm	Copper, tin plated	0.5 mm ²
50 pcs	Blade receptacle 4.8 mm	Copper, tin plated	0.5 mm ²
30 pcs	Blade receptacle 6.3 mm	Copper, tin plated	1.5 mm ²
60 pcs	Flat plug 2.8 mm	Copper, tin plated	0.5 mm ²
50 pcs	Flat plug 4.8 mm	Copper, tin plated	0.5 mm ²
30 pcs	Flat plug 6.3 mm	Copper, tin plated	1.5 mm ²
60 pcs	Isolating sleeve transparent 2.8 mm	PVC	11
50 pcs	Isolating sleeve transparent 4.8 mm	PVC	//
30 pcs	Isolating sleeve transparent 6.3 mm	PVC	//

Connection only by qualified electricians!