

Heat Shrink Tube Assortments 2:1 (100 pcs) Item-No.: 22CA167

This range of shrinking tubes is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 100 pieces of shrinking ratio 2:1 standard shrinking tube for a range of application diameter from 1.5 to 18 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used. High quality product from industrial applications.



Technical Specifications

Material: PE • Shrink temperature (min.): 70 °C • Shrink temperature (max.): 110 °C • Operating temperature: -40 °C to +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 1.5 kV (30 sec.) • Flammability: VW-1 • Rated voltage: 600 V • Volume resistivity: min. $10^{14} \Omega$ • Elongation break: min. 300% • Industrial quality.

All hoses comply with RoHS directives and are halogen-free. Further technical data on the components included, are printed on the inside of the covers.

Content

5 pieces - Ø 12 mm - length 65 mm • 3 pieces - Ø 18 mm - length 95 mm • 4 pieces - Ø 15 mm - length 95 mm • 25 pieces - Ø 3 mm - length 32 mm • 30 pieces - Ø 1.5 mm - length 32 mm • 8 pieces - Ø 9 mm - length 65 mm • 15 pieces - Ø 4.5 mm length - 32 mm • 10 pieces - Ø 6 mm length - 65 mm.