

PRO HOLDER Adapter

Art.-No.**GA-IGM12-45****Description**

angled length 55 mm Internal thread M12

Features

Connection M12 × 1.5 (6h) L = 10 mm

Mounting surface Ø 36 mm

Rotation prevention by 2 × M5 thread

In connection with base total angle of inclination 90°

Fits on ball pin M12 × 1.5

Machine steel, chrome-plated

Made in Germany

Orientation dimensions (H×W×D) 61 × 36 × 36 mm

Weight 313 g

**Application and technical data**

Angle adapter for PRO HOLDER mounting bracket with ball joint. This adapter allows an angle of inclination of 90 degrees, for horizontal or vertical alignment of the clamped workpieces or devices. In connection with the ball joint holder please note, especially for safety-relevant parts, that we cannot give a guarantee of the holding forces without knowing your specific application. The ball may behave differently under different physical conditions than it does in our test laboratory in an optimal test environment. Our product development department is constantly working on the optimisation and further development of our products. If you have any questions, improvements or suggestions, we look forward to hearing from you.

Detail drawing