

PRO HOLDER extension

Art.-No.	VL-IGM6-050
Description	straightlength 50 mm Internal thread M6

Features

Connection M6 × 1 (6h) L = 10.5 mm

Mounting surface Ø 36 mm

Rotation prevention by 2 × M5 thread

Counterface SW32

Fits on ball pin M12 × 1.5

Aluminum

Made in Germany

Orientation dimensions (H×W×D) 50 × 36 × 36 mm

Weight 131 g



Application and technical data

Extension for the PRO HOLDER mounting bracket with ball joint. Available in 50 or 100 mm, allow a larger distance to the ball joint or to achieve a larger working radius when aligning the clamped workpieces or devices. In connection with the ball joint holder please note, especially for safety-relevant parts, that we cannot give a guarantee of the holding forces without knowing your specific application. The ball may behave differently under different physical conditions than it does in our test laboratory in an optimal test environment. Our product development department is constantly working on the optimisation and further development of our products. If you have any questions, improvements or suggestions, we look forward to hearing from you.

Detail drawing

