

TESTEC ACTIVE DIFFERENTIAL PROBES

TT-SX 9001 / TT-SX 9002



	TT-SX 9001	TT-SX 9002
Order Number	15601	15602
Attenuation Ratio	x10 / x100	x 20 / x200
DC-Accuracy	$\pm 2\%$	$\pm 2\%$
Bandwidth (-3dB)	30 MHz	30 MHz
Max. Differential Input Voltage (DC + peak AC)	$\pm 70\text{ V @ x10}$ $\pm 700\text{ V @ x100}$	$\pm 140\text{ V @ x200}$ $\pm 1400\text{ V @ x200}$
Max. Common Mode Input Voltage (DC + peak AC)	$\pm 70\text{ V @ x10}$ $\pm 700\text{ V @ x100}$	$\pm 140\text{ V @ x20}$ $\pm 1400\text{ V @ x200}$
Absolute Maximum Input Voltage (each side to ground)	1000V CAT III	
Safety Standard	IEC1010-031:2015 – CAT III – cTUVus certified	
Power requirements	4 x AA batteries or USB-C cable	