



**Sikringskassett, Lav spenning, 40 A, AC 600 V, DC 300 V, 300 kA, 26 x 29 x 55 mm, CF, J, 1P, UL, CSA, fingersikker, Langsom**



**Type** CUBEFUSE, TCF 40A IND  
**Catalog No.** TCF40

Illustrasjon lik

## Leveringsprogram

Produktspekter			Smeltesikring
Basisfunksjon			Sikringskassett
Bruksområde			Lav spenning
Nominell strøm	I	A	40
Nominell spenning			AC 600 V DC 300 V
Størrelse			26 x 29 x 55 mm
Brukkategori			CF J
Beskrivelse			fingersikker
Bryteevne		kA	300
Antall poler			1P
kan brukes før størrelse/applikasjoner			Elektriske tavler, industriell kontroll, frakoblingsbrytere for maskineri, påkrevde fingerbeskyttelsessystemer
Utløsningsegenskaper	Klasse		Langsom
Standard/Godkjenning			UL CSA
Standarder/Regulations			UL-listet CSA Certified
Langsom			tidsforsinkelse 10 sekunder (minimum) ved 500 % av nominell strøm

## Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			Other
Nominal rated current		A	40
Nominal rated voltage		V	600
Utilization category			Other
Type of fuse status indicator			None