



Sikringskassett, Lav spenning, 25 A, AC 500 V, 120 kA, NH000, gL/gG, IEC, dual indikator, strømførende gripehåndtak



Type **NH FUSE 25AMP 500V SIZE 000 GG MGL**
 Catalog No. **25NHG000B**

EL-Nummer **1664006**

Leveringsprogram

Produktspekter			Smeltesikring
Basisfunksjon			Sikringskassett
Bruksområde			Lav spenning
Nominell strøm	I	A	25
Nominell spenning			AC 500 V
Konstruksjonsstørrelse			NH000
Brukskategori			gL/gG
Statusindikator			dual indikator
Beskrivelse			strømførende gripehåndtak
Bryteevne		kA	120
kan brukes for størrelse/applikasjoner			industriell
Standard/Godkjenning			IEC
Form			firkantet med knivbladkontakter som flukter i endene
Standarder/Regulations			IEC 60269-2 smeltesikringsystem A DIN 43620 VDE 0636-2

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			NH000
Nominal rated current		A	25
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator