



Sikringskassett, Lav spenning, 80 A, AC 500 V, 120 kA, NH01, gL/gG, IEC, dual indikator, strømførende gripehåndtak



Type NH FUSE 80A 500V GG/GL SIZE 01
Catalog No. 80NHG01B

EL-Nummer 1664044

Leveringsprogram

Produktspekter			Smeltesikring
Basisfunksjon			Sikringskassett
Bruksområde			Lav spenning
Nominell strøm	I	A	80
Nominell spenning			AC 500 V
Konstruksjonsstørrelse			NH01
Brukskategori			gL/gG
Statusindikator			dual indikator
Beskrivelse			strømførende gripehåndtak
Bryteevne		kA	120
kan brukes for størrelse/applikasjoner			industriell
Standard/Godkjenning			IEC
Form			firkantet med knivbladkontakter som flukter i endene
Standarder/Regulations			IEC 60269-2 smeltesikringsystem A DIN 43620 VDE 0636-2

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecI@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			Other
Nominal rated current		A	80
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator