



Trykknapp, 250V, 16A, 1 L+1 Å

Type **Z-PU/SO**
Catalog No. **276293**

Tekniske data etter ETIM 8.0

Devices for distribution board-/surface mounting (EG000062) / Trykknapp for DIN-skinne (EC001546)

Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Push button for distribution board (ec1@ss10.0.1-27-14-23-02 [AFZ814014])

Antall NC-kontakter			1
Antall NO-kontakter			1
Antall vekselkontakter			0
Brytestrøm			16
Vekselspenning			250
Spenningsstype			AC
Med signallampe			Nei
Hettefarge			Andre
Lampetype			LED
Lampesokkel			Andre
Maks lampeeffekt			0
Lampespenning			0 - 0
Farge på knapp			Svart
Bredde i antall modulmellomrom			1
Innbyggingsdybde			60
Beskyttelsesklasse IP			IP40