



**Load Shedding relé**

**Type** Z-LAR32-S  
**Catalog No.** 248261

Illustrasjon lik

**Tekniske data etter ETIM 8.0**

Devices for distribution board-/surface mounting (EG000062) / Strømréle (EC001655)		
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Load shedding relay for distribution board (ecl@ss10.0.1-27-14-23-32 [ACN383011])		
Merkespenning		250
Merkestrømsområde lu		15 - 32
Startstrømsområde		15 - 32
Maks utkoblingsforsinkelse		0
Maks kontinuerlig strøm		32
Antall NO-kontakter		1
Antall NC-kontakter		0
Antall vekselkontakter		0
Merkestrøm (styrekontakter)		1
Maks brytespenning (styrekontakter)		250
Maks bryteeffekt (styrekontakter)		7.36
Elektrisk levetid (styrekontakter)		100000
Mekanisk levetid (styrekontakter)		0
Maks. elektrisk koblingsfrekvens		3600
Spenningsstype		AC
Monteringsmetode		DIN-skinne
Bredde i antall modulmellomrom		1
Innbyggingsdybde		60
Beskyttelsesklasse IP		IP20