



Sikringsholder, Lav spenning, 30 A, AC 600 V, 10 x 38 mm, CC, 1P, UL



Type
Catalog No.

1Pole 30A 600V MFH For 10X38 Class CC
CHCC1DU

Leveringsprogram

Produktspekter			Smeltesikring tilbehør
Basisfunksjon			Sikringsholder
Bruksområde			Lav spenning
Nominell strøm	I	A	30
Nominell spenning			AC 600 V
Størrelse			10 x 38 mm
Brukskategori			CC
Beskrivelse			DIN-skinne montering fargekodet Normert for bruk med 75 °C eller 90 °C ledning flettet ledning reserveklemmer og med kamsamleskinner Bruk en kabel som er beregnet for høyere temperatur med passende belastningsreduksjon. modulær
Antall poler			1P
kan brukes for størrelse/applikasjoner			for sylindersikringskassetter
Standard/Godkjennelse			UL
Standarder/Regulations			IEC cULus CCC CSA UR

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss8.1-27-14-21-21 [AD1305004])			
For fuse size			10x38 mm
Number of poles			1
Concurrently switching N-neutral			No