

DATABLAD - 3POLE 30A 600V MFH FOR 10X38 MIDGET FUSE



Sikringsholder, Lav spenning, 32 A, AC 690 V, 10 x 38 mm, 3P, UL, IEC

Type
Catalog No.

3Pole 30A 600V MFH For 10X38 Midget fuse
CHM3DU



Leveringsprogram

Produktspekter			Smeltesikring tilbehør
Basisfunksjon			Sikringsholder
Bruksområde			Lav spenning
Nominell strøm	I	A	32
Nominell spenning			AC 690 V
Størrelse			10 x 38 mm
Beskrivelse			DIN-skinne fargekodet Normert for bruk med 75 °C eller 90 °C ledning flettet ledning reserveklemmer og med kamsamleskinner Bruk en kabel som er beregnet for høyere temperatur med passende belastningsreduksjon. modulær
Antall poler			3P
kan brukes for størrelse/applikasjoner			for sylindersikringskassetter
Standard/Godkjennelse			UL IEC
Standarder/Regulations			IEC cULus CCC CSA UR

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss8.1-27-14-21-21 [ADI305004])		
For fuse size		10x38 mm
Number of poles		3
Concurrently switching N-neutral		No