

Product fiche

Delegated Regulation (EU) 812/2013

Supplier name or trademark	SYGONIX
Model identifier	2623641
Declared load profile	XXS
Water heating energy efficiency class	A
Water heating energy efficiency	37 %
Annual electricity consumption	489 kWh
Annual fuel consumption	- GJ
Other Information	
Thermostat temperature settings	no setting
Sound power level (Indoors)	15 dB
Specific precautions	<p>1.No upside down and tilt installation is required. This product must be erected vertically. 2.At the first use, the water source must be connected before the power supply ;Do the same after water is cut off. 3.The water in the appliance may be frozen, and electricity is prohibited at that time. 4.This appliance cannot be installed outside or in places where it may freeze. 5.The maximum water temperature should not exceed 50# when used. 6.Do not put towel and other articles on the plug, socket and this appliance,don't use your wet hand to pull the plug 7.Do not use this product with other high power household appliances when the power capacity is low. (For example rice cookers, electric iron, air conditioners, vacuum cleaners and microwave ovens). 8.The outlet shall not be connected to any non specified faucet or connector and any choke element. 9.Spray cap must be descaled regularly.</p>

Model placed on the Union market from 01/11/2022.



EPREL registration number: 1391830

<https://eprel.ec.europa.eu/qr/1391830>

Supplier: Conrad Electronic SE (Importer)

Website:

Customer care service:

Name: Conrad Electronic SE

Website:

Email: product.support@conrad.de

Phone: 09622300

Address:

Klaus-Conrad-Str. 1
92240 Hirschau
Germany