



# Multipower Combo+ US

Powerful 48 W PD charging of 2 USB devices  
(1 x USB & 1 x USB C) + USB C Cable



Charge your USB devices super fast with Power Delivery Technology

## Laptop Ready

This Multipower Combo+ US USB AC PD Charger from SKROSS® conveniently ensures a full battery, charging up to 2 USB devices (1 x USB and 1 x USB C device) simultaneously with 48 W of power. Compatible in more than 50 destinations with the US socket standard, it is easily able to power up laptops, smartphones, tablets, audio devices and more, ultra-fast. Also includes 1 x USB C cable (160 cm) for easy charging of your USB C powered devices such as a laptop.

### Suitable for



### Compatibility (Output)



USA/Japan

### Packaging (Retail)



### Product Category

- PD USB Wall Charger

### Technical Specifications

- Suitable in all countries with US socket standard
- 1 x 48 W PD Wall Charger (1 x USB Type-C + 1 x USB Type-A) + USB C Cable (160 cm)
- 2 USB ports for simultaneous powerful charging
- **Single Port Output**  
1 x USB Type-C (PD) Output: 5.0 V DC / Max. 3.0 A, 9.0 V DC / Max. 3.0 A, 12.0 V DC / Max. 3.0 A, 15.0 V DC / Max. 3.0 A, 20.0 V DC / Max. 2.4 A, Max. 48.0 W  
1 x USB Type-A (QC 3.0) Output: 3.6 – 6.0 V DC / Max. 3.0 A, 6.0 – 9.0 V DC, Max. 2.0 A, 9.0 – 12.0 V DC, Max. 1.5 A, Max. 18.0 W
- **Double Port Output**  
1 x USB Type-C (PD) Output: 5.0 V DC / Max. 3.0 A, 9.0 V DC / Max. 3.0 A, 12.0 V DC / Max. 2.5 A, 15.0 V DC / Max. 2.0 A, 20.0 V DC / Max. 1.5 A, Max. 30.0 W  
1 x USB Type-A (QC 3.0) Output: 3.6 – 6.0 V DC / Max. 3.0 A, 6.0 – 9.0 V DC, Max. 2.0 A, 9.0 – 12.0 V DC, Max. 1.5 A, Max. 18.0 W  
Average active efficiency: 82.47%, Efficiency at low load (10 %): 73.43 %, No-load power consumption: 0.06 W
- USB output: Max. 48.0 W in total
- Input voltage: 100 V – 240 V~, 50/60 Hz, Max. 1200 mA, Max. 288 W

### Weight

- Charger + cable: 177 g
- Charger + cable + packaging: 230 g

### Dimensions

- Charger: W 30 mm H 81 mm D 60 mm, Cable: H 1600 mm
- Charger + cable + packaging: W 92 mm H 185 mm D 40 mm

### Packaging Unit

- Master retail: 20 pcs | Inner carton: 10 pcs
- Dimensions master retail: TBC

### Standard Colour

- White

Description	Article-No.	EAN-Code	Made in China
Multipower Combo+ US, retail, white	SKKT000348WPDUSCCN	7640166326366	