VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

UC-1XCX004
USB CHARGER 20 W

CE

Item no: 2631643

The product is a USB charger. The product has charging ports of the following types:
USB-C® (supports power delivery fast charge PD3.0)



TECHNICAL DATA

Data according to EU regulation 2019/1782

Manufacturer	Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau
Commercial registration number	HRB 3896
Model identifier	UC-1XCX004
Input voltage	100 - 240 V/AC
Input AC frequency	50 / 60 Hz
Output voltage Output current Output power	5.0 V/DC, 3.0 A, max. 15.0 W 9.0 V/DC, 2.22 A, max. 20.0 W 12.0 V/DC, 1.67 A, max. 20.0 W
Average active efficiency	85.5 %
Efficiency at low load (10 %)	76.0 %
No-load power consumption	0.09 W

Environment

Operating temperature	0 to +35 °C
Operating humidity	5 - 90 % RH (non-condensing)
Storage temperature	-20 to +70 °C
Storage humidity	0 - 95 % RH (non-condensing)

Others

Dimensions (W x H x D) (approx.)	42 x 29 x 81 mm
Weight (approx.)	55 g

CONTENTS

Product // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2631643_V1_0926_en_ds 3300965387 I1/O1 en