

# LogiLink®

## Wireless 2-way Smart Plugs with 2 USB Ports

Art. No.: SH0102



### Build Your Smart Home

Manage appliances and USB devices, such as lamps, kettle, chargers or television via free smartphone app using Wi-Fi connection.



### App Remote Control

Smart Plug can be controlled through your existing Wi-Fi network via the free [Smart Life](#) or [Megos Smart Home](#) app.



Smart Life



Megos Smart Home

Download the free APP from the App Store or Google Play store.



Wi-Fi  
2.4 GHz



230 V/10 A  
2400 W



2-Port USB  
12 W



Over Current  
Protection



IP20



With Safety  
Shutter



### Power and Charge Multiple Devices

Provide 2 smart sockets and 2 USB fast charging ports. Able to control individually or collectively with schedules or timer.

\*USB ports are controlled in a group.



### Control Your Appliances from Anywhere

Turn on/off connected appliances wherever you are through your smartphone at any time.



### Works with Amazon Alexa and Google Home

Manage your home devices through voice control to make your life effortless.

## Specifications:

Wireless Standard	IEEE 802.11b/g/n
Wireless Frequency Range	2.412–2.472 MHz
Max. Transmission Power	100 mW
Operation Distance (In Open Area)	100–300 m
Rated Voltage	230 V AC 50/60 Hz, 10 A
Max. Output Power	2400 W
Plug	Safety plug CEE 7/7
Sockets	2x German sockets CEE 7/3
USB Power Output	5 V 2,4 A (12 W max. for 2 ports)
Safety Shutter	Yes
Protections	Over-current and over-voltage, over-temperature and short circuit protections
Protection Class	IP20
Operating Temperature	-20–55°C
Operating Humidity	45–75% RH (non-condensing)
Color	White
Product Dimension	13,5 x 6,5 x 7,9 cm
Product Weight	182 g
System Requirements	Android 5 or above / iOS 11 or above

## Package Contents:

- » 1x Wi-Fi 2-way Smart Plugs
- » 1x User Manual

## Package Information:

- » Packing Dimension: 137 x 68 x 82 mm
- » Packing Weight: 0,247 kg
- » Carton Dimension: 390 x 290 x 470 mm
- » Carton Q'ty: 50 pcs
- » Carton Weight: 13,15 kg



ⓘ Do not plug in a row ⓘ Only operate within the limits of the rated load

\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



SH0102



4 052792 066753

Made in China