

## VOLTCRAFT – TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

## MS-20SF FUSE FINDER



Item no. 2633263

The fuse finder enables the easy search and identification of the current fuses associated with the plug-in socket in the electrical home and residential installation. The set consists of a transmitter that modulates a coded signal on the live current path and a receiver. The transmitter is simply plugged into a live socket and the corresponding circuit breaker in the fuse box can be determined contact-free with the receiver.

### FEATURES

Quickly find the right fuse // For live systems and circuits // Visual and acoustic signal display // Contact-free search in the fuse box

### TECHNICAL DATA

#### a) Transmitter

Operating voltage	230 V/AC, 50 Hz
Protection class	I
Current consumption	<20 mA
Voltage measuring range	230 V/AC, 50 Hz
Overvoltage category	CAT II 250 V
Measurements (W x H x D)	118 x 60 x 35 mm

#### b) Receiver

Battery operation	9 V block battery
Voltage measuring range	230 V/AC, 50 Hz
Protection class	II
Overvoltage category	CAT III 250 V
Measurements (W x H x D)	195 x 36 x 55 mm



### c) General

Operating temperature	0 to +40 °C
Operating humidity	<80 % RH (non-condensing)
Storage temperature	0 to +50 °C
Storage humidity	<95 % RH (non-condensing)
Weight	218 g (Receiver + Transmitter)

### EQUIPMENT

Pulse LED // Receiving LED // Operating LED // Reset the receiving signal via one button press // LED and audible indications of low battery

### PACKAGE CONTENTS

Transmitter // Receiver // 9 V Block battery // Pouch // Operating instructions