2234095-2 ✔ ACTIVE

AMP

TE Internal #: 2234095-2

Applicators, Pneumatic Feed, OCEAN, Male Adapter Post - Atlantic Style Interface, 30 mm (1.12") Stroke Terminator / 40 mm (1.62") Stroke Terminator

View on TE.com >

Application Tooling > Applicators



Applicator Feed Type: **Pneumatic**

Applicator & Product Style: **OCEAN**

Application Interface: **Male Adapter Post - Atlantic Style**

Terminator Type: **30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator**

Wire Crimp Width: **1.07 mm [.042 in]**

Features

Termination Features

Wire Crimp Form	F

Dimensions

Wire Crimp Width	1.07 mm[.042 in]
Insulation Diameter Range	1.52 mm[.06 in]

Other

Applicator Feed Type	Pneumatic
Applicator & Product Style	OCEAN
Application Interface	Male Adapter Post - Atlantic Style
Terminator Type	30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator
Service Options	Capability Study, Crimped Samples, Cross Section - Photograph
Alignment Aids	Alignment Gauge, Camera

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 1-104480-7
SHORT POINT CONT PLTD SN




TE Part # 104480-4
SHORT POINT CONT 30 DPLX STMPD



TE Part # 1-104480-3
SHORT POINT CONT 30 DPLX STMPD LF



TE Part # 1-104480-2
SHORT POINT CONT 15 DPLX STMPD LF



TE Part # 104480-3
SHORT POINT CONT 15 DPLX STMPD




TE Part # 2217000-1
G II CE TERMINATOR




TE Part # 2161500-1
AMP 5K/40 CE TERMINATOR




TE Part # 1633966-6
CRIMPER,INSULATION O



TE Part # 690463-1
FLOATING SHEAR




TE Part # 2280441-1
INSERT SHEAR, REAR CARRIER



TE Part # 1803095-3
FLOATING SHEAR, FRONT



TE Part # 2119806-1
INSERT, SHEAR




TE Part # 104480-2
SHORT POINT CONT PLTD SN-PB



TE Part # 1633860-4
CRIMPER, WIRE F



TE Part # 2119862-1
SHEAR HOLDER, REAR



TE Part # 2161400-5
AMP 3K/40 CE EL TERMINATOR



TE Part # 2161500-2
AMP 5K/40 CE TERMINATOR, W/CQM



TE Part # 2161700-4
5K CE STRIPPING MODULE



TE Part # 2161700-5
5K CE STRIPPING MODULE W/ CQM




TE Part # 2217000-2
MODEL G II CE TERMINATOR, W /CQM


Customers Also Bought



TE Part #281698-5
HEADER HE14 RA 5 P




TE Part #776430-1
AS 16, 3P CAP ASSY, KEY 1




TE Part #4-100103-0
40P.A/L.STRAIN REL.




TE Part #166052-1
TD 20 F CRIMP SOCKET WIRE SIZE



TE Part #2-1761606-9
IDC LOW PRO HDR 26P VERT LG LA



TE Part #4-215882-0
40 WAY GREY MK II RECP



TE Part #776299-1
ASSEMBLY SOCKET LOOSE PC GOLD



TE Part #1625826-3
TL2B R01 1%



TE Part #1060-16-0988
PIN, SF, SIZE 16, 14-18, PD/NI/AU

Documents

Product Drawings

OCEAN-2.0-APPLICATOR-SA

English

Datasheets & Catalog Pages

TE_APPLICATORS_CATALOG

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English