DTT-20-03 ✔ ACTIVE

DEUTSCH

TE Internal #: DTT-20-03

Hand Crimping Tools, Commercial Crimp Tooling, Operator Releasable & Adjustable, Fixed In Tool, Manual, Straight Action Hand Tool

View on TE.com >

Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Fixed In Tool**

TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Features

Other

Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Fixed In Tool
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Straight Action Hand Tool

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # CAT-D48-SFT273
DEUTSCH STAMPED & FORMED CONTACTS

Customers Also Bought



TE Part #2138852-3
MOUNTING CLIP, 3MM PANEL, AMPSEAL 16 HL



TE Part #2-2176381-5
RQ 0805 22K1 0.1% 10PPM 5K RL




TE Part #1062-20-0622
SOC, SF, SIZE 20, 14-16, NI/NI



TE Part #1028-021-0205
BKSHL, 2P, BLK, REC, ST, NW 7.5/8.5



TE Part #2292865-2
AS16 BACKSHELL, 12P CAP, NC20, MC



TE Part #58637-2
PRO-CRIMP DIE 20-14 UMNL



TE Part #1676249-2
RN 0805 20K5 0.1% 10PPM 1KRL



TE Part #180-DTP04
BKSHL, 4P, BLK, PLG, ST, SIDE AB, NW 16



TE Part #2103744-1
PLUG, HVIL ONLY, KEY A, HVA280-2PHI SE

TE Part #4-1579016-0
ERGOCRIMP DIE SET MCP1.5K

Documents

Product Drawings

CRIMP TOOL

English

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English