# 2-1579024-5 ✔ ACTIVE

AMP

TE Internal #: 2-1579024-5

Hand Crimping Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), Manual

View on TE.com >

Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

## Features

### Other

| | |
|---|---|
| Crimp Form-Wire Barrel Type | Open Barrel - F Crimp |
| Tool Grade | Premium Crimp Tooling |
| Ratchet Configuration | Not Releasable, Not Adjustable |
| Die Sets Type | Fixed In Tool |
| Specification Type | TE Product Specification (114-) |
| TE Certification | Cannot be Certified |
| Power Technology Type | Manual |
| Tooling Type | CERTI-CRIMP II, Straight Action Hand Tool |

## Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |

| | |
|---|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## Compatible Parts



TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET


TE Part # 1-929963-3
STIFTKONTAKT 2,5MMD

TE Part # 1-929970-3
BU-KONTAKT 2,5MMD


TE Part # 1-929980-1
STIFTKONTAKT 1,5MMD

TE Part # 1-929980-2
STIFTKONTAKT 1,5MMD


TE Part # 1-929980-3
STIFTKONTAKT 1,5MMD



TE Part # 1-962967-0
2,5MM STIFTKONTAKT



TE Part # 8-929970-3
2,5MM BU-KONTAKT




TE Part # 929963-5
STIFTKONTAKT 2,5MMD

TE Part # 929963-6
STIFTKONTAKT 2,5MMD



TE Part # 929970-5
BU-KONTAKT 2,5MMD




TE Part # 929970-6
BU-KONTAKT 2,5MMD

TE Part # 962967-2
STIFTKONTAKT 2,5MMD

TE Part # 962967-4
STIFTKONTAKT 2,5MMD


TE Part # 962967-7
2,5MM STIFTKONTAKT




TE Part # 962967-8
2,5MM PIN CONTACT LP (0,5-1,0)

TE Part # 962967-9
2,5MM STIFTKONTAKT

TE Part # 962977-2
2,5MMD SOCKET CONTACT



TE Part # 962977-7
2,5MM BU-KONTAKT



TE Part # 962977-8
2,5MM SOCKET CONTACT LP(>0,5-1,0)

## Customers Also Bought




TE Part #YDTS26W25-37SAV001
PLUG ASSY



TE Part #YDTS26Z21-16SNV001
PLUG ASSY




TE Part #5053332035
RNF-100-1-9-STK



TE Part #829098-000
322A412-25-0





TE Part #2387332-1
SDE F 2.5mm CONTACT 0.35-1.0mm2 ASSY



TE Part #NB18044001
RNF-100-1-1/2-WH-SP

TE Part #1579024-5
HT33-SDE HAND TOOL 1.5, 2.5 DIA. CONTACT



TE Part #057275-000
234A932-25/86-0



TE Part #1579024-3
HT11K HAND TOOL 1.5, 2.5 DIA. CONTACTS

TE Part #4-1579014-1
HT11K HAND TOOL MCON050, 0.13-0.35 SQ.MM

## Documents

## Product Drawings

### HAND TOOL 2,5 MM DIA. CONTACTS 0,5-1,0

English

## Datasheets & Catalog Pages

### Bottoming Dies

English