

69911 ✓ ACTIVE

AMP

TE Internal #: 69911

Hand Crimping Tools, Premium Crimp Tooling, Removable /Interchangeable, TE Product Specification (114-) / MIL Spec, Hydraulic / Battery / Manual

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

Power Technology Type: **Battery, Hydraulic, Manual**

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1752786-1  
 HYP10 4/0-1000MCM 26T HEAD



TE Part # 69082  
 HYP8 4/0-1000MCM 26T HEAD

### Customers Also Bought



TE Part #52937  
 PIDG Short Spring Spade Tongue Terminals



TE Part #53241-1  
 PG SPR SPD 22-16COMM 22-18MIL8



TE Part #8-2176416-7  
 9W STD M/OX 5% 200K



TE Part #324449  
 SPLICE,AMPOWER PARA 350MCM




TE Part #36932  
 BODY SOLIS RING 4/0 3/8



TE Part #321875  
 TERMINAL,SOLIS R 3/0 3/8



TE Part #48176  
 CRIMP JAW NEST



TE Part #F60545-000  
 CI-253-TVL

### Documents

**Product Drawings**

HYP8/10 SOLIS 250-300MCM 69082 DIE SET



English

---

**Datasheets & Catalog Pages**

**AT-Hydraulic Crimp Tooling Solutions-1654519**

English

**Bottoming Dies**

English

---

**Instruction Sheets**

**Instruction Sheet (U.S.)**

English