1-454766-1 ✔ ACTIVE

AMP

TE Internal #: 1-454766-1

Spare & Wear Tooling, Heavy Duty Mini (HDM)

View on TE.com >

Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **Heavy Duty Mini (HDM)**

Features

Other

Applicator & Product Style	Heavy Duty Mini (HDM)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 466790-4
HDMCBSSAPR283 343 K


Customers Also Bought



TE Part #917067-6
040-2 TAB CONT S GOLD 22-18




TE Part #3-2112780-3
18POS, MIXED,REC HSG,ASSY, SEALED



TE Part #173858-4
070 MULTILOCK CAP ASSY 12P GRN




TE Part #2151144-1
OCEAN_2.0_APPLICATOR-S-067F062F




TE Part #1333225-1
ANVIL, COMBINATION SPECIAL



TE Part #2-2119582-7
Crimper, Insulation F Premium



TE Part #184394-1
2X2 PLG ASY W/RET W/O CPA C3-A



TE Part #172217-1
FF 250 REC HSG 2P NYLON NAT



TE Part #2-2151494-1
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part #CP4904-000
ES2000-NO.1-C1-0-65MM-SH

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English