



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: Heavy Duty Mini (HDM)

Features

Other

Applicator & Product Style	Heavy Duty Mini (HDM)
----------------------------	-----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1852621-3
HDM SMPR042F G (CUT)

TE Part # 567334-2
HDM DULSMPR042F K

Customers Also Bought

TE Part #776534-2
AS 16, 2P CAP ASSY, RD, KEY 2

TE Part #DT04-6P-E005
REC, 6P, BLK, N, CAP

TE Part #776492-2
SOC, SF, SIZE 16, 14-18 AWG, NI/SN

TE Part #174259-2
ECONO-J MK-2 CAP HSG 4P

TE Part #66255-6
MALE CONTACT ASSY. (STRIP)

TE Part #208652-1
SEALING CAP ASSY, SZ 17, CPC

TE Part #DT3P-DC
PROTECT CVR, 3P, REC, GRY, DT

TE Part #HD10-3-96P
SQ FG REC ASM

TE Part #1-66358-0
III+ SKT, 18-14, 30AU/FL, STRIP

TE Part #171661-2
E-J MK-2 070 TAB CONT

Documents

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets
Instruction Sheet (U.S.)

English

