



Application Tooling > Spare & Wear Tooling



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2-2151186-1
OCEAN_2.0_Applicator-S-070F118O



TE Part # 2-2151186-2
OCEAN_2.0_Applicator-S-070F118OA



TE Part # 2151186-1
OCEAN_2.0_Applicator-S-070F118O



TE Part # 2151186-2
OCEAN_2.0_Applicator-S-070F118OA




TE Part # 7-2151186-7
OCEAN_2.0_SPARE_PART_KIT-070F118O

Customers Also Bought



TE Part #2271180-1
PLUG, 2PIN WIRE TO WIRE CONNECTOR



TE Part #60793-1
SHUR PLUG .180 18-14 AWG TPBR



TE Part #2822344-4
MINI MLC CAP HSG ASSY 7P



TE Part #2-456408-8
CRIMPER WIRE .110 "F"



TE Part #1-456403-3
CRIMPER WIRE .062 F



TE Part #1338125-7
CRIMPER, WIRE, SPLICE



TE Part #3-1333225-9
ANVIL, COMB., SPECIAL



TE Part #8-1333201-3
ANVIL, COMBINATION .055



TE Part #1-464962-0
ANVIL, COMBINATION



TE Part #238009-1
BLOCK, CRIMPER SPACER (.130)

Documents



Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION
English

Instruction Sheets
Instruction Sheet (U.S.)
English