



Application Tooling &gt; Spare &amp; Wear Tooling



Applicator &amp; Product Style: OCEAN

## Features

### Other

Applicator & Product Style	OCEAN
----------------------------	-------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2016 (169) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2-2151180-1  
OCEAN\_2.0\_Applicator-S-080F130F



TE Part # 2151180-1  
OCEAN\_2.0\_Applicator-S-080F130F



TE Part # 2151180-2  
OCEAN\_2.0\_Applicator-S-080F130FA


## Customers Also Bought



TE Part #D369-R99-NP0  
369 9 WAY REC, NO CONTACTS, PIN




TE Part #5053134034  
RNF-100-1/4-9-SP



TE Part #2-160967-1  
CABLE TY 98X2.5 NAT



TE Part #1722386-8  
FLOATING SHEAR, FRONT



TE Part #2302454-2  
1-PORT MATENET FRAME,UTP, COD B




TE Part #8-1722359-6  
SHEAR HOLDER, FRONT



TE Part #1-1583690-1  
CRIMPER, INSULATION "O"(.120")



TE Part #1-1722368-7  
GUIDING, DEPRESSOR WIRE



TE Part #1803415-1  
WIRE DEPRESSOR



TE Part #8-1722359-8  
DEPRESSOR, SHEAR

## Documents

### Datasheets & Catalog Pages

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

