



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 2836265-2 OCEAN_2.0_Applicator-S-116F232O	 TE Part # 2-2151625-2 OC-PA-S-FA-210F343O-030-0318	 TE Part # 2-2151781-2 OC-PA-S-FA-156F431O-001-0211	 TE Part # 2-2151951-2 OCEAN_2.0_APPLICATION-S-157F244OV
 TE Part # 2-2151991-2 OCEAN_2.0_Applicator-S-120F265O	 TE Part # 2-2266257-2 OC-PA-S-FA-210F390O-001-0404	 TE Part # 2-2266455-2 OCEAN_2.0_Applicator-S-110F150OV	 TE Part # 2-2266539-2 OC-PA-S-FA-218F402O-023-0699
 TE Part # 2-2266614-2 OC-PA-S-FA-152F260O-030-0745	 TE Part # 2-2266617-2 OCEAN_2.0_APPLICATION-S-140F270O	 TE Part # 2-2266822-2 OCEAN_2.0_APPLICATION-S-100F174OA	 TE Part # 2-2266962-1 OCEAN_2.0_APPLICATION-S-130F264O
 TE Part # 2-2266962-2 OCEAN_2.0_APPLICATION-S-130F264O	 TE Part # 2-2266994-2 OC-PA-S-FA-211F291OV-030-0318	 TE Part # 2-2836055-2 OCEAN_2.0_Applicator-S-165F244OV	 TE Part # 2-2836079-2 OCEAN-2.0-APPLICATION-S-190F409O
 TE Part # 2-2836231-2 OC-PA-S-FA-157F256O-023-0656	 TE Part # 2-2836249-2 OCEAN-2.0-APPLICATION-S-157F260O	 TE Part # 2-2836265-2 OCEAN_2.0_Applicator-S-116F232O	 TE Part # 2-2836298-2 OC-PA-S-FA-152F270O-030-1464

Customers Also Bought



 TE Part #3-456135-4 CRIMPER INSULATION O	 CRIMPER REPRESENTATION ONLY TE Part #1803248-3 CRIMPER, INSULATION O PREMIUM	 ANVIL REPRESENTATION ONLY TE Part #2-1633922-7 ANVIL, COMBINATION	 TE Part #3-1803019-0 CRIMPER, INSULATION O
 CRIMPER REPRESENTATION ONLY TE Part #3-456407-8 CRIMPER, WIRE .100 "F"	 ANVIL REPRESENTATION ONLY TE Part #7-1633928-5 ANVIL COMBINATION	TE Part #3-22280-3 SPRING, COMPRESSION	TE Part #1-1463053-0 HOLDER, TERMINAL
TE Part #2-2168083-0 SCREW, CAP, HEX SOCKET HD, MET	 TE Part #690471-9 COMB ANVIL		

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English