



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2-2151410-2 OCEAN_2.0_Applicator-S-140F203F	 TE Part # 2-2151723-2 OC-PA-S-FA-153F375O-030-0124	 TE Part # 2-2151825-2 OC-PA-S-FA-210F280O-040-0342	 TE Part # 2-2151841-2 OCEAN_2.0_APPLICATION-S-160F280O
 TE Part # 2-2151927-2 OCEAN_2.0_APPLICATION-S-165F244OV	 TE Part # 2-2266164-2 OCEAN_2.0_Applicator-S-217F272OV	 TE Part # 2-2266472-1 OC-PA-S-FM-110F263O-061-0443	 TE Part # 2-2266472-2 OC-PA-S-FA-110F263O-061-0443
 TE Part # 2-2266583-2 OCEAN_2.0_APPLICATION-S-165F244OV	 TE Part # 2-2266764-1 OC-PA-S-FM-120F220O-105-1440	 TE Part # 2-2266764-2 OC-PA-S-FA-120F220O-105-1440	 TE Part # 2-2836038-2 OCEAN_2.0_APPLICATION-S-209F272F
 TE Part # 2-2836046-2 OC-PA-S-FA-210F343O-030-1464	 TE Part # 2-2836052-2 OCEAN_2.0_Applicator-S-217F323OV	 TE Part # 2-2836079-2 OCEAN-2.0-APPLICATION-S-190F409O	 TE Part # 2-2836648-2 OC-PA-S-FA-120F276O-138-1526
 TE Part # 2-2836775-2 OCEAN_2.0_Applicator-S-217F323OV	 TE Part # 2-2836992-2 OC-PA-S-FA-147F173F-156-1555	 TE Part # 2-2837439-2 OCEAN-2.0-APPLICATION-S-157F272OA	 TE Part # 2-2837790-2 OCEAN-2.0-APPLICATION-S-200F310O

Customers Also Bought



TE Part #318707-1
FLOATING SHEAR



ANVIL REPRESENTATION ONLY
TE Part #2-1633930-8
ANVIL,COMBINATION



TE Part #3-1333281-6
CRIMPER, WIRE, F PREMIUM



CRIMPER REPRESENTATION ONLY
TE Part #3-1803365-1
CRIMPER, INSULATION O



TE Part #5-1633609-9
CRIMPER, WIRE F



ANVIL REPRESENTATION ONLY
TE Part #5-1633920-3
ANVIL, COMBINATION



ANVIL REPRESENTATION ONLY
TE Part #6-1633928-4
ANVIL COMBINATION



ANVIL REPRESENTATION ONLY
TE Part #6-1803056-4
ANVIL



CRIMPER REPRESENTATION ONLY
TE Part #7-1333281-2
CRIMPER, WIRE, F PREMIUM



KIT REPRESENTATION ONLY
TE Part #7-2266450-7
OCEAN_2.0_SPARE_PART_KIT-061F079O

Documents

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets
Instruction Sheet (U.S.)

English