1-454765-2 ✔ ACTIVE

AMP

TE Internal #: 1-454765-2

Spare & Wear Tooling, OCEAN

View on TE.com >

Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **OCEAN**

Features

Other

Applicator & Product Style	OCEAN

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 466789-4
HDMCBSSAPR222 272 K



TE Part # 466789-5
HDM*CBS* 5SMPR222 G



TE Part # 466789-3
HDMCBSSAPR 222 272T

Customers Also Bought



TE Part #6609031-3
2ER1 M0=F7179



TE Part #DTM1312PA12PCR008
HDR, 24P, BLK, RA EEC, NI/CU, AC



TE Part #2150380-2
OCEAN_2.0_APPLICATOR-E-110F160FA




TE Part #2150386-2
OCEAN_2.0_APPLICATOR-E-090F140F



TE Part #2151017-2
OCEAN_2.0_APPLICATOR-S-048F080FA




TE Part #7-2150086-7
OCEAN_2.0_SPARE_PART_KIT-090F100F



TE Part #7-2150693-7
OCEAN_2.0_SPARE_PART_KIT-110F155F



TE Part #7-2151122-7
OCEAN_2.0_SPARE_PART_KIT-062F110F



TE Part #933568-1
MTA 156 FEED TRACK W CRIMP HEAD PROD



TE Part #6-1393114-3
KUHP-1A51-240=KU

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English