690588-1 ✔ ACTIVE

AMP

TE Internal #: 690588-1

Spare & Wear Tooling, OCEAN

View on TE.com >

Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **OCEAN**

Features

Other

Applicator & Product Style	OCEAN

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1852633-1
EAPOHB160TABLOCK180O LM/G-HINGE BAR



TE Part # 1852895-1
HDM EMPO K-HINGE BAR



TE Part # 1855041-1
HINDGE BAR F.A. EMPO160TAB180O LM & G



TE Part # 1855465-1
HDM w/FA HINGE BAR EAPR160TAB-LOCK180O



TE Part # 1855468-1
HDM/FA/HB EMPO160TABLOCK180O LM & G



TE Part # 1855601-1
HDM/FA EAPRHB.160TABLOC.180O G CUT



TE Part # 567303-1
APPL,HINGE BAR 9EMPO160T180O T



TE Part # 567408-2
HDMHB 9EAPR160T180O G



TE Part # 680194-3
HDM*HB* 9EAPR160T180O G



TE Part # 680563-1
HDM 9EMPO140T140O T&G



TE Part # 680563-2
HDM 9HBEAPR140T140O K




TE Part # 680588-3
HDM 9HBAPR1405140OG



TE Part # 687390-5
M HBEAPR140T140OK



TE Part # 687394-5
M HBEAPR140T140OK



TE Part # 7-1855041-7
SPARE PART KIT

TE Part # 1852633-2
EAPRHB160TABLOCK180O K - HINGE BAR



TE Part # 297530-2
MINI APLICADOR END FEED

TE Part # 680563-3
HDM/FA EF A HB 140TAB LOCK 170O BCH G




TE Part # 687390-1
M HBEMPO140T140OT



TE Part # 687391-1
M HBEMPO140T140OT

Customers Also Bought




TE Part #908917-1
ANVIL,INSERT



TE Part #2-2119582-4
Crimper, Insulation F Premium




TE Part #4-456406-7
CRIMPER, WIRE .090 F



TE Part #690718-1
ANVIL-REVERSIBLE



TE Part #1-2217206-0
Blade, Slug



TE Part #454709-1
ANVIL INSERT



TE Part #690482-4
FRONT SHEAR PLATE



TE Part #690569-1
FRONT SHEAR PLATE



TE Part #240644-1
PLATE-REAR SHEAR



TE Part #690569-3
FRONT SHEAR PLATE

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English