



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-T4827-T273 TIMER, RECEPTACLE AND TAB	 CRIMPER REPRESENTATION ONLY TE Part # 456408-2 CRIMPER WIRE .110 F	 CRIMPER REPRESENTATION ONLY TE Part # 2119785-6 CRIMPER, INSUL OVERLAP PREM	 TE Part # 2-2151391-2 OC-PA-S-FA-110F140OV-001-0199
 TE Part # 2151391-2 OC-AT-S-FA-110F140OV-001-0199	 ANVIL REPRESENTATION ONLY TE Part # 3-1333207-1 ANVIL, COMBINATION .110	 TE Part # 927849-1 STC REC 6.3 Contact SRC Sn	

Customers Also Bought

 TE Part #2-1418506-2 AMP MCP 6.3 REC. 2 POS HSG	 TE Part #2323101-5 5POS,TAB0.5X0.4,HEADER ASSY,90 DEG	 TE Part #CV67226001 ATUM-24/8-2-30MM	 TE Part #2150706-1 OCEAN_2.0_Applicator-E-094F134F
 TE Part #2266090-1 OCEAN_2.0_Applicator-S-070F100O	 TE Part #2266923-1 OC-AT-S-FM-062F090F-111-0298	 TE Part #7-2150393-7 OCEAN_2.0_SPARE_PART_KIT-170F224F	 KIT REPRESENTATION ONLY TE Part #7-2151318-7 OC-039F042O-CRIMPTOOLINGKIT
 TE Part #7-2266115-7 OCEAN_2.0_SPARE_PART_KIT-103F080O	 TE Part #708817-1 7 E 95-35 CU		



Documents

Product Drawings

OC-110F140OV-CRIMPTOOLINGKIT

English

Instruction Sheets

Instruction Sheet (U.S.)

English