



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # CAT-T4827-T273 TIMER, RECEPTACLE AND TAB	 CRIMPER REPRESENTATION ONLY TE Part # 1-2119784-8 CRIMPER, INSUL O PREMIUM	 CRIMPER REPRESENTATION ONLY TE Part # 1-456403-3 CRIMPER WIRE .062 F	 ANVIL REPRESENTATION ONLY TE Part # 1333202-1 ANVIL, COMBINATION .062
 TE Part # 2-2151050-1 OCEAN_2.0_APPLICATOR-S-062F0900	 TE Part # 2-2151050-2 OCEAN_2.0_APPLICATOR-S-062F0900	 TE Part # 2151050-1 OCEAN_2.0_APPLICATOR-S-062F0900	 TE Part # 2151050-2 OCEAN_2.0_APPLICATOR-S-062F0900
 TE Part # 5-2151050-1 OCEAN_2.0_APPLICATOR-S-062F0900	 TE Part # 5-2151050-2 OCEAN_2.0_APPLICATOR-S-062F0900		

Customers Also Bought

 TE Part #2151050-2 OCEAN_2.0_APPLICATOR-S-062F0900	 ANVIL REPRESENTATION ONLY TE Part #5-1633919-9 ANVIL COMBINATION	 TE Part #5-456404-5 CRIMPER, WIRE .070 F	 TE Part #7-2151036-7 OCEAN_2.0_SPARE_PART_KIT-055F072O
 TE Part #7-2151200-7 OCEAN_2.0_SPARE_PART_KIT-070F-0900	 TE Part #7-2151268-7 OCEAN_2.0_SPARE_PART_KIT-062F155O	 TE Part #7-1579028-3 LOCKING TOOL 10POL	 TE Part #1752356-7 SUPPORT, TERMINAL



Documents

Product Drawings

OCEAN_2.0_SPARE_PART_KIT-062F090O

English

Instruction Sheets

Instruction Sheet (U.S.)

English