



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

|                            |       |
|----------------------------|-------|
| Applicator & Product Style | OCEAN |
|----------------------------|-------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Out of Scope                                                                                                                   |
| EU ELV Directive 2000/53/EC                   | Out of Scope                                                                                                                   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JAN 2022 (223)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-M8793-T273  
MQS, RECEPTACLE AND TAB

**CRIMPER** REPRESENTATION ONLY

TE Part # 1-1633966-0  
CRIMPER, INSULATION O

**ANVIL** REPRESENTATION ONLY

TE Part # 1633135-9  
ANVIL, COMBINATION .120

TE Part # 2-2151051-1  
OCEAN\_2.0\_Applicator-S-120F155O

TE Part # 2-2151051-2  
OCEAN\_2.0\_Applicator-S-120F155O

TE Part # 2151051-1  
OCEAN\_2.0\_Applicator-S-120F155O

TE Part # 2151051-2  
OCEAN\_2.0\_Applicator-S-120F155O

**CRIMPER** REPRESENTATION ONLY

TE Part # 5-562108-1  
WIRE CRIMPER

TE Part # 7-2151051-1  
OCEAN\_2.0\_Applicator-S-120F155O

TE Part # 7-2151051-2  
OCEAN\_2.0\_Applicator-S-120F155O

Customers Also Bought

TE Part # CV16886001  
Single Wall RNF-100 Stick HS Tubing

**CRIMPER** REPRESENTATION ONLY

TE Part # 1803246-7  
CRIMPER, INSULATION F PREMIUM

**ANVIL** REPRESENTATION ONLY

TE Part # 7-1803171-3  
ANVIL

TE Part # 7-2151577-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-100F165O

Documents

Product Drawings  
[OCEAN\\_2.0\\_SPARE\\_PART\\_KIT-120F155O](#)

English

Instruction Sheets  
[Instruction Sheet \(U.S.\)](#)

English

