



PANTILO OVAL PD

E27 pendant light, white/chrome

With its elegant glass shade, the PANTILO OVAL PD has a radiant and unique design. The chrome version conjures up an atmospheric lighting environment. The 2.5 m cable can be shortened and is compatible with almost all installation heights. The open cable end allows the creation of a group of lights, which makes this cylindrical pendant light a genuine highlight for catering businesses, hotels or larger living spaces.

TECHNICAL DATA

| | |
|-------------------------|-------------------|
| Item no. | 1006402 |
| Socket | E27 |
| Number of sockets | 1 |
| IP Code | IP 20 |
| Assembly details | Ceiling with Acc. |
| Primary nominal voltage | 200-240V ~50/60Hz |
| Safety class | II |
| Wattage | 15 W |
| Color | white |
| Height | 28.5 cm |
| Diameter | 18 cm |
| Pendant length | 250 cm |
| Net weight | 1 kg |
| Gross weight | 1.07 kg |

Recommended lamp

| | |
|---------|---|
| 1005265 | ST64 E27 , gold LED light, 7.5W 2500K CRI90 320° |
| 1005301 | A60 E27 , white LED light, 9W 2700K CRI90 220° |
| 1005304 | A60 E27 , Frosted LED light, 7.5W 2700K CRI90 320° |
| 1005318 | A60 E27 RGBW smart , white / milky LED light, 9W CRI90 230° |

Accessories

| | |
|---------|---|
| 1001542 | PENDANT ADAPTER , for 240V 3-circuit track, traffic white, incl. installation accessories |
| 1002163 | FITU single canopy , soft gold |
| 1004744 | FITU , ceiling rose black |
| 1004745 | FITU , ceiling rose white |
| 1004746 | FITU , ceiling rose chrome |
| 132600 | CEILING PLATE FITU , single ceiling plate, round, black, incl. strain-relief |
| 132601 | CEILING PLATE FITU , single ceiling plate, round, white, incl. strain-relief |
| 132605 | CEILING PLATE FITU , single ceiling plate, round, chrome, incl. strain-relief |
| 143120 | PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, black, incl. strain relief and threaded piece |
| 143121 | PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, white, incl. strain relief and threaded piece |

| | |
|--------|---|
| 143124 | PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, silver-grey, incl. strain re- lief and threaded piece |
| 145990 | PENDANT ADAPTER , for 240V 3-phase track, black, incl. installation ac- cessories |
| 145994 | PENDANT ADAPTER , for 240V 3-phase track, grey, incl. installation ac- cessories |