



LED light

QPAR111 GU10 12W 750lm 4000K CRI90 55° dimmable

The dimmable LED light with GU10 fitting and QPAR111 shape has a CRI of over 90, 750 lumen, a beam angle of 55 degrees, a colour temperature of 4000 Kelvin, and its service life of 40,000 hours makes it extremely sustainable.

TECHNICAL DATA

Item no.	1005299
Socket	GU10
Lamp type	QPAR111
IP Code	IP 20
Dimmable	Yes
Dimming technology	Leading edge, trailing edge
Lamp mercury content	0 mg
Nominal voltage	220-240V ~50/60Hz V
Weighted energy consumption	12 kWh/1000h
Wattage	12 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	40 °C
Lumen	750 lm
Colour temperature	4000 Kelvin
Beam angle	55 °
Color	aluminium
CRI	90
Lumen	0.96 lm
Binning	6 SDCM
Service life	40000 h
Switching cycles	20000
Risk Group	1

Light Source

1304097	
---------	---

Width	11 cm
Height	7 cm
Depth	11 cm
Diameter	11 cm
Net weight	0.19 kg
Gross weight	0.203 kg