



M-POL 60 Pole

Bollard, anthracite, 53.4cm

DALI-compatible for professional outdoor projects: the aluminium M-POL 60 Pole can be controlled via the digital interface and is designed to be highly modular. Variable lamp heads and diffusers ensure a wide range of applications. The colour temperature (2700/3000K) can be selected via the CCT switch before installation. Thanks to its IP65 protection class rating, the anthracite bollard light is ideally protected against penetration by dirt or moisture. With an impact rating of IK10, it can also withstand significant shocks. Installation via the connection box is totally straightforward.

TECHNICAL DATA

Item no.	1006380
Color	anthracite
Height	53.4 cm
Diameter	12.4 cm
Net weight	2.052 kg
Gross weight	2.196 kg

Accessories

1006382	M-POL ground anchor , stainless steel
1006383	M-POL M Polehead , Lamp head, anthracite, 11W, 470/510lm, 2700/3000K, CRI90
1006384	M-POL M Polehead , Lamp head, anthracite, 11W, 590/660lm, 2700/3000K, CRI90
1006385	M-POL S Polehead , Lou- ver lamp head, anthra- cite, 11W, 145/155lm, 2700/3000K, CRI90
1006386	M-POL M Polehead , Louver lamp head, an- thracite, 11W, 190/210lm, 2700/3000K, CRI90
1006387	M-POL S Polehead , Shader lamp head, an- thracite, 11W, 285/310lm, 2700/3000K, CRI90
1006388	M-POL M Polehead , Shader lamp head, an- thracite, 11W, 420/460lm, 2700/3000K, CRI90
1006389	M-POL S Polehead , Lamp head, anthracite, 19W, 890/950lm, 2700/3000K, CRI90, DA- LI
1006390	M-POL M Polehead , Lamp head, anthracite, 19W, 1150/1230lm, 2700/3000K, CRI90, DA- LI
1006391	M-POL S Polehead , Lou- ver lamp head, anthra- cite, 19W, 260/270lm, 2700/3000K, CRI90, DA- LI
1006392	M-POL M Polehead , Louver lamp head, an- thracite, 19W, 350/370lm, 2700/3000K, CRI90, DA- LI

1006393	M-POL S Polehead , Shader lamp head, an- thracite, 19W, 520/550lm, 2700/3000K, CRI90, DA- LI
1006394	M-POL M Polehead , Shader lamp head, an- thracite, 19W, 820/870lm, 2700/3000K, CRI90, DA- LI
1006453	Connection box , 5-pin, IP68, black, DALI
228726	T-CONNECTION BOX , black, IP68
228730	CONNECTION BOX , 3-pin, IP68