DATASHEET


Circular Connector, Wire to Wire, Straight Female Plug and Pin Socket 2 Contacts / M12


Item no.: 2705564

Version 10/23









Dimension: mm±0.2

Specification

Number of Contacts: 2 Mating thread type: M12

Material

Shell: Nickel plated Zinc Alloy Insulation: Black Bakelite Contact: Silver plated Copper

Electrical

Operating voltage: 250V Rated current: 4 A

Insulation resistance: $100~M\Omega$ min. Contact resistance: $10~m\Omega$ max.

Environment

Operation temperature: -20 to 85°C

Protect class: IP55 Termination: Solder

Suit Cable size: O.D. ø5mm max.

Wire guide: AWG 22 - 20

Conductor cross-section: 0.34 - 0.5mm²