

60pcs Plastic Cable Gland Set PG Thread, White

Item No. 2102CA113



Specification

Material:

Gland - PA 66


Seal - NBR

Color: White (RAL 9010)


Thread type: PG

Waterproof class: IP68

Working temperature: -20 ~ 80°C



* Washer and Locking Nut are including in set



Thread	Cable range (ømm)	TD (ømm)	TL (mm)	GL (mm)	GD (ømm)	Pcs.
PG7	3.0 ~ 6.5	12.5	9.0	20.2	17.0	15
PG9	4.0 ~ 8.0	15.0	9.0	22.5	20.8	12
PG13.5	6.0 ~ 12.0	20.1	9.0	26.5	25.9	10
PG16	10.0 ~ 14.0	22.2	10.0	27.0	29.0	9
PG21	13.0 ~ 18.0	28.0	12.0	30.6	35.8	8
PG25	16.0 ~ 21.0	30.0	12.0	33.5	38.0	6