


BU-P72973

(SMA Flange Mount Connector, Female to Female)



- The BU-P72973 is a female to female SMA flange mount connector. High bandwidth and durability for confident connections.
- Overall length 0.87" (22.2mm), overall width 0.5" (12.7mm)
- Holes are spaced 0.34" (8.6mm) center-to-center.

Material: Body Gold-plated brass

Contacts Gold-plated beryllium copper

Insulator PTFE

• Rating: Frequency Range 0 to 18 GHz

Voltage Hands-free testing to 500 VRMS Max.

Toll Free: 800.955.2629

Phone: 330.780.2525 Fax: 330.780.2524

Impedance 50 Ohms

Temperature -50°C (-58°F) to 105°C (221°F)

RoHS 3 compliant