



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Locking & Mounting



D-Shaped Connector Accessories: **Captive Pan Head Screw**

Screw Length: 19.05 mm [.75 in]

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Captive Pan Head Screw

Mechanical Attachment

Screw & Hole Thread Size	4-40 UNC 2A
Screw Length	19.05 mm[.75 in]

Dimensions

Thread Length	6.35 mm[.25 in]
---------------	-----------------

Operation/Application

For Use With	ACTION PIN™ Connector, CHAMP Latch Low Profile Connectors, Right Angle PCB Connectors
--------------	---

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 229974-1
ASSY, PLUG, 50 POS, B SLOT

Also in the Series | CHAMP Docking Connectors



D-Sub Covers(28)



D-Sub Locking & Mounting(29)



Docking Connector Guide Hardware(5)



Docking Connectors(31)



IDC D-Sub Connectors(79)



PCB D-Sub Connectors(1)


Customers Also Bought



TE Part #3-640620-2
02P MTA100 CONN ASSY F/T RED




TE Part #5148468-1
ASSY,PIN,EUOCARD,TYPE C,LEAD-FREE,144/1




TE Part #2-552496-1
90 DEG COVER KIT-64 POS BLK



TE Part #4-552008-1
KIT, COVER, 180, 50 POS



TE Part #344008-1
.250" SPEC.F.TAB (PLATED)




TE Part #3-644563-3
03P MTA100 CONN ASSY F/T 24AWG




TE Part #344075-1
2 WAY TAB HSG.



TE Part #2822353-1
250 TYPE RUBBER PLUG



TE Part #229909-1
COVER,TAPERED,90DEG"CHAMP PKG"



TE Part #229910-1
CLAMP, CABLE "CHAMP PACKAGING"

Documents

Product Drawings

SCREW,PAN HD,"CHAMP PACKAGING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5229911-1_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5229911-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5229911-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[MD_5229911-1_04182018254_dmtec](#)

English

[MD_5229911-1_04182018254_dmtec](#)

English